

**KEMET Part Number: 030MS22AAMA1STD**  
(A902GF030V220A)

MS/A902, Aluminum Electrolytic, 30 uF, -0/+25%, 220 VAC, -20/+60°C



General Information	
<b>Series:</b>	MS/A902
<b>Dielectric:</b>	Aluminum Electrolytic
<b>Description:</b>	Motor Start Aluminum Electrolytic
<b>RoHS:</b>	Yes
<b>Lead:</b>	Quick Connect
<b>AEC-Q200:</b>	No
<b>Halogen Free:</b>	Yes
<b>Shelf Life:</b>	156 Weeks

Dimensions	
<b>D</b>	38mm +/-0.5mm
<b>L</b>	75mm MAX

Packaging Specifications	
<b>Packaging:</b>	Bulk, Bag

Specifications	
<b>Capacitance:</b>	30 uF
<b>Capacitance Tolerance:</b>	-0/+25%
<b>Voltage AC:</b>	220 VAC
<b>Temperature Range:</b>	-20/+60°C
<b>Rated Temperature:</b>	60°C
<b>Life:</b>	500 Hrs