


KEMET Part Number: ALC80A271CD400
(A547DF271M400A)

ALC80, Aluminum Electrolytic, 270 uF, 20%, 400 VDC, -40/+105°C



General Information	
Series:	ALC80
Dielectric:	Aluminum Electrolytic
Description:	Snap-In, Aluminum Electrolytic
RoHS:	Yes
Lead:	2 Pin
AEC-Q200:	No
Halogen Free:	Yes
Notes:	Dimensions D And L Include Sleevings.
Shelf Life:	156 Weeks

Dimensions	
D	30mm +1mm
L	40mm +/-2mm
S	10mm +/-0.1mm
LL	6.3mm +/-1mm
F	2mm +/-0.1mm

Packaging Specifications	
Weight:	50 g
Sleevings:	Yes
Packaging:	Bulk, Bag

Specifications	
Capacitance:	270 uF
Capacitance Tolerance:	20%
Voltage DC:	400 VDC, 440 VDC (Surge)
Temperature Range:	-40/+105°C
Rated Temperature:	105°C
Life:	7000 Hrs (Rated Voltage And Ripple Current At 105C), 11000 Hrs (Rated Voltage At 105C)
Resistance:	448.4 mOhms (100Hz 20C), 228.9 mOhms (10kHz 20C)
Ripple Current:	1.738 Amps (100Hz 105C), 5.141 Amps (10kHz 105C)
Leakage Current:	324 uA (5min 20°C)