

KEMET Part Number: ALS30A473MF063
(A331PM473M063A)

ALS30, Aluminum Electrolytic, 47,000 uF, 20%, 63 VDC, -40/+85°C



General Information

Series:	ALS30
Dielectric:	Aluminum Electrolytic
Description:	Screw Terminal, Aluminum Electrolytic
RoHS:	Yes
AEC-Q200:	No
Notes:	Dimensions D And L Include Sleaving. MS (MxH) = M12x16. Mounting Clip (Sold Separately): V10/UTE2738
Shelf Life:	156 Weeks

Dimensions

D	66mm +/-1mm
L	105mm +/-2mm
T	5.5mm +/-0.5mm
S	28.5mm +/-0.5mm
DT	13mm +/-0.5mm
LT	110.5mm +/-1mm
TD	10mm MIN
V	15.8mm NOM
Z	10mm NOM

Packaging Specifications

Weight:	505 g
Sleaving:	Yes
Packaging:	Bulk, Box

Specifications

Capacitance:	47,000 uF
Capacitance Tolerance:	20%
Voltage DC:	63 VDC, 72.5 VDC (Surge)
Temperature Range:	-40/+85°C
Rated Temperature:	85°C
Life:	19000 Hrs (Rated Voltage And Ripple Current At 85C), 38000 Hrs (Rated Voltage At 85C)
Resistance:	8 mOhms (100Hz 20C), 7 mOhms (10kHz 20C)
Ripple Current:	26.7 Amps (100Hz 85C), 26.5 Amps (10kHz 85C)
Leakage Current:	6000 uA (5min 20°C)