


KEMET Part Number: ALS71A242KE350
(A490LH242M350A)

ALS71, Aluminum Electrolytic, 2,400 uF, 20%, 350 VDC, -40/+85°C



Dimensions	
D	51mm +/-1mm
L	82mm +/-2mm
T	5.5mm +/-0.5mm
S	22.2mm +/-0.5mm
DT	13mm +/-0.5mm
LT	86.5mm +/-1mm
TD	10mm MIN
V	13.7mm NOM
Z	10mm NOM

Packaging Specifications	
Weight:	220 g
Sleeving:	Yes
Packaging:	Tray

General Information	
Series:	ALS71
Dielectric:	Aluminum Electrolytic
Description:	Screw Terminal, Aluminum Electrolytic
RoHS:	Yes
Mounting:	Stud
AEC-Q200:	No
Halogen Free:	Yes
Notes:	Dimensions D And L Include Sleaving. MS (MxH) = M12x16. Mounting Clip (Sold Separately): V4/2737
Shelf Life:	156 Weeks

Specifications	
Capacitance:	2,400 uF
Capacitance Tolerance:	20%
Voltage DC:	350 VDC, 385 VDC (Surge)
Temperature Range:	-40/+85°C
Rated Temperature:	85°C
Life:	18000 Hrs (Rated Voltage And Ripple Current At 85C), 36000 Hrs (Rated Voltage At 85C)
Resistance:	80 mOhms (100Hz 20C), 49 mOhms (10kHz 20C)
Ripple Current:	8.1 Amps (100Hz 85C), 13.6 Amps (10kHz 85C)
Leakage Current:	5040 uA