


C20A, Film, Metallized Polypropylene, AC Filter, 15 uF, 10%, 640 VAC, 1400 VDC



Dimensions	
D	65mm +/-0.5mm
L	117mm +/-2mm
W	18mm +/-1mm
S	28mm +/-1mm

Packaging Specifications	
Mounting:	Bolt - M12x16
Packaging:	Bulk, Bag

General Information	
Series:	C20A
Dielectric:	Metallized Polypropylene
Style:	Can
Features:	Single Phase PFC
RoHS:	Yes
Lead:	Threaded Studs M10
AEC-Q200:	No
Miscellaneous:	Thermal Resistance = 14.1 C/W.
Notes:	This part is Not For New Design. See part number C44PRGR5150RASK.

Specifications	
Capacitance:	15 uF
Capacitance Tolerance:	10%
Voltage AC:	640 VAC
Voltage DC:	1400 VDC
Temperature Range:	-25/+70°C
Rated Temperature:	70°C
Insulation Resistance:	10 MOhms
Max dV/dt:	30 V/us
Resistance:	2.5 mOhms (10kHz)
Ripple Current:	35 Amps (10kHz 40C)
Inductance:	120 nH