


C44A, Film, Metallized Polypropylene, Power, 40 uF, 5%, 400 VAC, 700 VDC



Threaded Mounting Stud
 D < 55: M8x10
 D >= 55: M12x12,5

Dimensions	
D	65mm +/-0.5mm
L	138mm +/-2mm
S	22.3mm +/-0.5mm

Packaging Specifications	
Mounting:	Bolt - M12x12.5
Packaging:	Bulk, Bag
Packaging Quantity:	12

General Information	
Series:	C44A
Dielectric:	Metallized Polypropylene
Style:	Can
RoHS:	Yes
Lead:	Threaded Studs M6
AEC-Q200:	No
Miscellaneous:	Thermal Resistance = 4 C/W.

Specifications	
Capacitance:	40 uF
Capacitance Tolerance:	5%
Voltage AC:	400 VAC
Voltage DC:	700 VDC
Temperature Range:	-40/+85°C
Rated Temperature:	70°C
Max dV/dt:	35 V/us
Resistance:	4 mOhms (TYP)
Ripple Current:	32 Amps, 1200 Amps (Peak)