


KEMET Part Number: GMC10.2224K50A31TR16
(F115WP224K050V)



GMC/F115, Film, Metallized PEN, General Purpose, 0.22 uF, 10%, 30 VAC, 50 VDC, 100°C, 4036, 5.5mm



Note: '()' correspond to the letters used in the product bulletin

Dimensions	
Chip Size	4036
L	10.2mm +/-0.2mm
W	9.1mm +/-0.2mm
T	5.5mm +/-0.2mm
F	0.5mm NOM

Packaging Specifications	
Packaging:	T&R
Packaging Quantity:	800

General Information	
Series:	GMC/F115
Dielectric:	Metallized PEN
Style:	SMD Chip
RoHS:	Yes
AEC-Q200:	No
Shelf Life:	104 Weeks
MSL:	3

Specifications	
Capacitance:	0.22 uF
Capacitance Tolerance:	10%
Voltage AC:	30 VAC
Voltage DC:	50 VDC
Temperature Range:	-55/+125°C
Rated Temperature:	100°C
Dissipation Factor:	0.6% 1kHz, 1% 10kHz, 2.5% 100kHz
Insulation Resistance:	10 GOhms
Max dV/dt:	20 V/us

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

