


KEMET Part Number: FC0V474ZFTBR24
(USCFC00V474ZBC)

FC, Supercapacitors, SMD Can, 0.47 F, -20/+80%, 3.5 VDC, V-Chip



Dimensions

D	10.5mm +/-0.5mm
L	8.5mm MAX
W	10.8mm +/-0.2mm
S	5mm NOM
G	0mm +0.3/-0.1mm
LT1	1.2mm +/-0.1mm
LT2	3.6mm +0.5mm

Packaging Specifications

Lead:	V-Chip
Weight:	1.4 g
Packaging:	T&R, 380mm

General Information

Series:	FC
Description:	Surface Mount Double Layer Capacitor
Features:	Ultra Low ESR, High Power Pulse
RoHS:	Yes
AEC-Q200:	No

Specifications

Capacitance:	0.47 F
Capacitance Tolerance:	-20/+80%
Voltage DC:	3.5 VDC
Temperature Range:	-25/+70°C
Rated Temperature:	70°C
Resistance:	25000 mOhms (1kHz)
Ripple Current:	0.42 mAmps (30min)