

KEMET, FLLD4-TH, EMI/RFI Filters, Noise Suppression, 520 VAC, 25 A, 130x125x115mm

General Information

Series:	FLLD4-TH
Style:	Chassis Mount
Description:	EMI Filter, Chassis Mount, Compact
Features:	Three Phase, High Performance
RoHS:	Yes
Qualifications:	IEC/EN 60939
Lead:	Threaded Studs M6

Dimensions

L	130mm NOM
W	125mm NOM
H	115mm NOM
L1	90mm NOM
W1	137.5mm NOM
W2	153mm NOM
J	32mm NOM
K	6.5mm NOM
M (Earth)	Threaded Studs M6
Lead	Threaded Studs M6

Specifications

Voltage AC:	520 VAC, 300 VAC
Rated Frequency:	50-60 Hz
Ripple Current:	25 A (50°C)
Rated Temperature:	50°C
Temperature Range:	-25/+100°C
Climate Category:	25/100/21
Test Voltage DC (P to P):	2250 VDC
Test Voltage DC (P to E):	3000 VDC
Voltage:	2250 VDC (Test P to P), 3000 VDC (Test P to E)
Power Loss:	12 W (25°C 50 Hz)
Leakage Current:	11 mA

Packaging Specifications

Packaging:	Bulk
Packaging Quantity:	1
Weight:	1.2 kg