


KEMET Part Number: MPCH0730LR24
(UPIC0730LR2400)

KEMET
a YAGEO company

KEMET, MPCH, Power, 0.24 uH, 20%, 0730(2711)



General Information	
Series:	MPCH
Style:	SMD
Chip Size:	0730(2711)
Description:	Shielded, Surface Mount Inductor
Features:	Large Current Inductors
RoHS:	Yes
Core:	Composite
Miscellaneous:	40 (K) Temperature Rise Max.

Dimensions	
L	8mm MAX
W	6.7mm +/-0.3mm
T	3mm MAX
LL	1.5mm NOM
G	2mm +/-0.3mm

Specifications	
Inductance:	0.24 uH (0.1 MHz)
Inductance Tolerance:	20%
Temperature Range:	-40/+125°C
Rated Temperature:	120°C
Shielded:	Yes
Current:	19 A (Isat, 20% Drop In Inductance), 23 A (Irms, 40C Rise By Self Heating)
DC Resistance:	1.2 mOhms

Packaging Specifications	
Packaging:	T&R, 330mm
Packaging Quantity:	1000

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

KEMET
a YAGEO company