


**KEMET Part Number: NBL15602S**  
(UPCNBL15602S00)



KEMET, NBL, Transducers, Single-layer



Dimensions	
D	15mm NOM
L	40.8mm NOM

Packaging Specifications	
Weight:	30
Packaging:	Bulk Tray, Box
Packaging Quantity:	160

General Information	
Style:	Bolt-On
Description:	Langevin Bolt-On Transducers
RoHS:	With Exemptions
SCIP Number:	6629125f-50d3-4e75-ae76-25e0bc1955b0
Notes:	Straight Construction.

Specifications	
Series:	NBL
Capacitance:	850 pF
Resonant Frequency:	60 kHz
Dynamic Admittance:	25msec
Mechanical Q:	500 Qm
Allowable Velocity:	50 cm/S
Allowable Power:	2.5
Temperature Range:	-40/+120°C

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

