


KEMET Part Number: PMR210MB5220M100R30 **Not for New Design**
(P410QM223M250AH101)



PMR210, Film, Metallized Paper, Resistor/Capacitor, 0.022 uF, 20%, 1000 VDC, 85°C, Lead Spacing = 15.2mm



Dimensions

Dimension	Value
L	18.5mm MAX
H	13mm MAX
T	7.3mm MAX
S	15.2mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	400

General Information

Series:	PMR210
Dielectric:	Metallized Paper
Style:	Radial
Features:	RC Unit approved
RoHS:	Yes
Lead:	Wire Leads
Qualifications:	ENEC, UL, cUL
AEC-Q200:	No
Construction:	Molded
Component Weight:	2.7 g
Miscellaneous:	Resistor= 100 Ohms.
Notes:	Not For New Design, Please Use The New P410 Series @ 300 VAC.

Specifications

Capacitance:	0.022 uF
Capacitance Tolerance:	20%
Voltage AC:	250 VAC
Voltage DC:	1000 VDC
Temperature Range:	-40/+85°C
Rated Temperature:	85°C
Insulation Resistance:	3 GOhms
Safety Class:	X1

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

