

KEMET Part Number: R46KW468050M2K
(46KW468050M2K)

R46 275 VAC, Film, Metallized Polypropylene, Safety, 6.8 uF, 10%, 275 VAC (X2), 560 VDC, 110°C, Lead Spacing = 37.5mm



Dimensions

L	41.5mm +0.3/-0.7mm
H	40mm +0.1/-0.7mm
T	20mm +0.3/-0.7mm
S	37.5mm +/-0.4mm
LL	25mm +2/-1mm
F	1mm +/-0.05mm

Packaging Specifications

Packaging:	Tray
Packaging Quantity:	84

General Information

Series:	R46 275 VAC
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	EMI Safety
RoHS:	Yes
Lead:	Wire Leads
Safety Class:	X2
Qualifications:	ENEC, UL, cUL, CQC
AEC-Q200:	No
Notes:	We Recommended To Use R46 @ 310 VAC.

Specifications

Capacitance:	6.8 uF
Capacitance Tolerance:	10%
Voltage AC:	275 VAC (X2)
Voltage DC:	560 VDC
Temperature Range:	-40/+110°C
Rated Temperature:	110°C
Dissipation Factor:	0.1% 1kHz
Insulation Resistance:	4.4118 GOhms
Max dV/dt:	100 V/us