

**KEMET Part Number: R474W410050A1K** Not for New Design  
(474W410050A1K)

**KEMET**  
a YAGEO company

R47 X1 440 VAC, Film, Metallized Polypropylene, Safety, 1 uF, 10%, 440 VAC (X1), 1000 VDC, 110°C, Lead Spacing = 37.5mm



General Information	
Series:	R47 X1 440 VAC
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	EMI Safety
RoHS:	Yes
Lead:	Wire Leads
Safety Class:	X1
Qualifications:	ENEC, UL, cUL
AEC-Q200:	No
THB Performance:	Yes

Dimensions	
L	41.5mm +0.3/-0.7mm
H	28.5mm +0.1/-0.7mm
T	16mm +0.3/-0.7mm
S	37.5mm +/-0.4mm
LL	25mm +2/-1mm
F	1mm +/-0.05mm

Specifications	
Capacitance:	1 uF
Capacitance Tolerance:	10%
Voltage AC:	440 VAC (X1)
Voltage DC:	1000 VDC
Temperature Range:	-40/+110°C
Rated Temperature:	110°C
Dissipation Factor:	0.1% 1kHz
Insulation Resistance:	30 GOhms
Max dV/dt:	150 V/us

Packaging Specifications	
Packaging:	Tray
Packaging Quantity:	108

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

**KEMET**  
a YAGEO company