


KEMET Part Number: SBCP-14HY103B
(UPIO14HY103B00)

KEMET
a YAGEO company

KEMET, SBCP-14HY, Power, 10000 uH, 10%, 5mm



Dimensions

Dimension	Value
D	12mm MAX
L	15mm MAX
S	5mm +/-0.5mm
LL	3.5mm +/-0.5mm
F	0.6mm NOM

Packaging Specifications

Component Weight:	6 g
Packaging:	Bulk
Packaging Quantity:	1500

General Information

Series:	SBCP-14HY
Style:	Through-Hole
Description:	Radial Leaded, Ferrite Power Inductors
Features:	DC-DC Converters, Nickel-Zinc (NiZn) Ferrite Core
RoHS:	Yes
Lead:	Wire Leads
Core:	Ferrite

Specifications

Inductance:	10000 uH
Inductance Tolerance:	10%
Temperature Range:	-20/+105°C
Shielded:	No
Current:	0.17 Amps
DC Resistance:	10.86 Ohms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

KEMET
a YAGEO company