


KEMET Part Number: SBCP-47HY100B
(UPIO47HY100B00)

KEMET

a YAGEO company

KEMET, SBCP-47HY, Power, 10 uH, 20%, 2.5mm



Dimensions

D	5mm MAX
L	7.5mm MAX
H	18mm +2mm
S	2.5mm +/-0.5mm
LL	3.5mm +/-0.5mm
F	0.5mm NOM

Packaging Specifications

Weight:	470 mg
Packaging:	Bulk
Packaging Quantity:	6000

General Information

Series:	SBCP-47HY
Style:	Through-Hole
Description:	Radial Leaded, Ferrite Power Inductors
Features:	DC-DC Converters, Nickel-Zinc (NiZn) Ferrite Core
RoHS:	Yes
Lead:	Wire Leads
Core:	Ferrite

Specifications

Inductance:	10 uH (0.01 MHz)
Inductance Tolerance:	20%
Temperature Range:	-20/+105°C
Shielded:	No
Current:	1.6 Amps
DC Resistance:	0.067 Ohms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

KEMET

a YAGEO company