


KEMET Part Number: SN14P-770H
(UALSN14P770H00)

KEMET
a YAGEO company

KEMET, SN, AC Line Filters, Normal Mode, 0.55 mH



Dimensions

D	34mm MAX
H	18.7mm MAX
LL	6.5mm +/-2mm
S	30mm NOM
L2	1.5mm MAX

Packaging Specifications

Packaging:	Bulk
Weight:	54 g

General Information

Series:	SN
Style:	Through-Hole
Features:	Compact Size
RoHS:	Yes
Miscellaneous:	Temperature Rise Maximum: 35 K

Specifications

Inductance:	550 uH (0.1 MHz)
Current:	3 A
Temperature Range:	-25/+105°C
DC Resistance:	0.085 mOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

KEMET
a YAGEO company