

**KEMET Part Number: SS-430L-W**  
(USES430LW00000)



KEMET, SS, Proximity, SMD, Pyroelectric Infrared, Detection Up To 3.5 Meters

#### General Information

<b>Series:</b>	SS
<b>Type:</b>	Proximity
<b>Style:</b>	SMD
<b>Description:</b>	Sensor Module with Lens: White
<b>Features:</b>	Detection Up To 3.5 Meters
<b>RoHS:</b>	With Exemptions
<b>REACH:</b>	SVHC (Pb – CAS 7439-92-1)
<b>Qualifications:</b>	REACH
<b>Field of View:</b>	Horizontal +/- 37 degree, Vertical +/-28 degrees

#### Dimensions

<b>L</b>	15mm NOM
<b>W</b>	15mm NOM

#### Packaging Specifications

<b>Packaging:</b>	Tray, Box
<b>Packaging Quantity:</b>	200
<b>Weight:</b>	800 mg

#### Specifications

<b>Temperature Range:</b>	-20/+60°C
<b>Voltage DC:</b>	3 VDC (Output, Detection), 0.0 VDC (Output, Non-Detection)
<b>Power Supply Voltage:</b>	3.5 -5.5 VDC
<b>Current:</b>	800 uA MAX (Consumption)
<b>Miscellaneous:</b>	Detection Output Voltage: 0.2 Seconds. Warm Up Time: 30 Sec (MAX).

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

