


KEMET Part Number: R11-244018-01 **Not for New Design**
(UAMR1102440180)



KEMET, R11, Acoustic Module, Multilayer



General Information	
Style:	Rubber Cased
Description:	Multilayer Piezoelectric Bimorph Actuator
RoHS:	With Exemptions
SCIP Number:	96933f00-7dd0-4e6d-8a13-be939072857c
REACH:	SVHC (PZT – CAS 12626-81-2)

Dimensions	
L	23.6mm MAX
W	4mm MAX
T	1.9mm MAX

Specifications	
Series:	R11
Capacitance:	1 uF
Capacitance Tolerance:	20%
Maximum Driving Voltage:	25 V Peak-Peak
Resonant Frequency:	6 kHz
Temperature Range:	-25/+70°C

Packaging Specifications	
Component Weight:	1.2
Packaging:	Bulk Tray, Box
Packaging Quantity:	1000

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

