


KEMET Part Number: SSHB10HS-R30015
(UALSB1SR300150)



a YAGEO company

KEMET, SSHB10HS, AC Line Filters, Dual Mode, 1.5 mH



Dimensions	
L	22mm MAX
T	17mm MAX
H	15.5mm MAX
LL	3.5mm +/-0.5mm
S	13mm +/-0.5mm
S1	10mm NOM
Wire Size	0.5mm

Packaging Specifications	
Packaging:	Tray
Packaging Quantity:	300
Weight:	10 g

General Information	
Series:	SSHB10HS
Style:	Through-Hole
RoHS:	Yes
Notes:	Marking: R30 Lot No.
Miscellaneous:	Temperature Rise Maximum: 60 K
Core:	Mn-Zn Ferrite

Specifications	
Voltage AC:	250 VAC
Inductance:	1.5 mH (10 kHz)
Current:	3 A
Temperature Range:	-25/+120°C
DC Resistance:	60 mOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.



a YAGEO company