


HV RAD-LDD Indust X7R HVHT200C, Ceramic, 0.022 uF, 10%, 500 VDC, X7R, Commercial, High Temperature, HighVoltage, Lead Spacing = 5.08mm



Dimensions	
L	8.13mm MAX
H	7.62mm MAX
T	6.35mm MAX
S	5.08mm +/-0.762mm
LL	3.175mm MIN
F	0.635mm +0.102/-0.051mm

Packaging Specifications	
Packaging:	Waffle
Packaging Quantity:	28

General Information	
Series:	HV RAD-LDD Indust X7R HVHT200C
Style:	Radial
Description:	Commercial, High Temperature, HighVoltage
Features:	Commercial
RoHS:	No
Prop 65:	⚠ WARNING: Cancer and reproductive harm - www.p65warnings.ca.gov .
REACH:	SVHC (Pb – CAS 7439-92-1)
Termination:	Copper
Failure Rate:	N/A
Testing and Reliability:	MIL-PRF-49467 Group A
Qualifications:	MIL-PRF-49467 Group A
AEC-Q200:	No

Specifications	
Capacitance:	0.022 uF
Capacitance Tolerance:	10%
Voltage DC:	500 VDC
Dielectric Withstanding Voltage:	750 VDC
Temperature Range:	-55/+200°C
Temperature Coefficient:	X7R
Aging Rate:	2% Loss/Decade Hour
Insulation Resistance:	45.454545 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.