


PHZ9004, Film, Metallized Polypropylene, Safety, 1 uF, 20%, 300 VAC, 110°C, 27.5mm



Note: '()' correspond to the letters used in the product bulletin

General Information	
Series:	PHZ9004
Dielectric:	Metallized Polypropylene
Style:	Dual-In-Line
Features:	EMI Safety (Three-Phase) not approved
RoHS:	Yes
Lead:	6 Leads
Safety Class:	EMI Class X2 for 3 Phase
AEC-Q200:	No
Miscellaneous:	3 x 1uF Capacitors In Parallel.

Dimensions	
L	64mm MAX
H	11.5mm MAX
T	30mm MAX
S	27.5mm +/-0.5mm
S1	27.5mm +/-0.5mm
LL	6mm -1mm
F	1mm +/-0.05mm

Specifications	
Capacitance:	1 uF
Capacitance Tolerance:	20%
Voltage AC:	300 VAC
Temperature Range:	-40/+110°C
Rated Temperature:	110°C
Dissipation Factor:	0.1% 1kHz, 0.5% 10kHz
Insulation Resistance:	10 GOhms
Max dV/dt:	100 V/us

Packaging Specifications	
Packaging:	Bulk, Bag
Packaging Quantity:	72

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.