


A755, Polymer Aluminum, 560 uF, 20%, 10 VDC, -55/+105°C, Lead Spacing = 3.5mm



Dimensions	
D	8mm +/-0.5mm
L	12mm +/-1mm
S	3.5mm +/-0.5mm
LL Negative	15mm MIN
LL Positive	19mm MIN
F	0.6mm +/-0.05mm

Packaging Specifications	
Packaging:	Bulk, Bag
Packaging Quantity:	500

General Information	
Series:	A755
Dielectric:	Polymer Aluminum
Description:	Single Ended, Polymer Aluminum
RoHS:	Yes
Lead:	Wire Leads
AEC-Q200:	No
Halogen Free:	Yes

Specifications	
Capacitance:	560 uF
Capacitance Tolerance:	20%
Voltage DC:	10 VDC, 11.5 VDC (Surge)
Temperature Range:	-55/+105°C
Rated Temperature:	105°C
Life:	5000 Hrs (+/-20% Initial Capacitance, 1.5x DF MAX, Leakage Within Limit)
Dissipation Factor:	10% 120Hz 20C
Resistance:	15 mOhms (100kHz 20C)
Ripple Current:	4820 mAmps (100kHz 105C)
Leakage Current:	840 uA (2min 20°C)