


A759, Polymer Aluminum, 150 uF, 20%, 63 VDC, -55/+125°C, Lead Spacing = 5mm



**Dimensions**

D	10mm +/-0.5mm
L	16mm +/-2mm
S	5mm +/-0.5mm
LL Negative	15mm MIN
LL Positive	19mm MIN
F	0.6mm +/-0.05mm

**Packaging Specifications**

Packaging:	Ammo
Packaging Quantity:	600

**General Information**

Series:	A759
Dielectric:	Polymer Aluminum
Description:	Single Ended, Polymer Aluminum
RoHS:	Yes
Lead:	Wire Leads
AEC-Q200:	No
Halogen Free:	Yes

**Specifications**

Capacitance:	150 uF
Capacitance Tolerance:	20%
Voltage DC:	63 VDC, 72.45 VDC (Surge)
Temperature Range:	-55/+125°C
Rated Temperature:	125°C
Life:	2000 Hrs (+/-20% Initial Capacitance, 1.5x DF MAX, Leakage Within Limit)
Dissipation Factor:	12% 120Hz 20C
Resistance:	48 mOhms (100kHz 20C)
Ripple Current:	2610 mAmps (100kHz 105C), 1520 mAmps (100kHz 125C)
Leakage Current:	1418 uA (2min 20°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.