


**KEMET Part Number: AE0203D08DF**  
(UPAE002030800D)

KEMET, AE, Piezo Actuators, Multilayer



#### Dimensions

<b>L</b>	100mm NOM
<b>W</b>	3mm +/-0.1mm
<b>W2</b>	3.4mm MAX
<b>H</b>	10mm +/-0.1mm
<b>T</b>	2mm +/-0.1mm
<b>T2</b>	2.4mm MAX

#### Packaging Specifications

<b>Weight:</b>	0.8
<b>Packaging:</b>	Bulk
<b>Packaging Quantity:</b>	10

#### General Information

<b>Style:</b>	Resin Coated
<b>Description:</b>	Resin Coated Type Multilayer Piezoelectric Actuators
<b>RoHS:</b>	With Exemptions
<b>REACH:</b>	SVHC (Pb – CAS 7439-92-1)
<b>Young's Modulus:</b>	4.4x10 <sup>10</sup> N/m <sup>2</sup>

#### Specifications

<b>Series:</b>	AE
<b>Displacement:</b>	9.1um +/-1.5um
<b>Voltage DC:</b>	150 VDC
<b>Capacitance:</b>	0.18 uF
<b>Capacitance Tolerance:</b>	20%
<b>Resonant Frequency:</b>	138 kHz
<b>Tensile Strength:</b>	20 N
<b>Generated Force:</b>	200 N
<b>Stiffness:</b>	22 N/um
<b>Insulation Resistance:</b>	100 MOhms
<b>Temperature Range:</b>	-25/+85°C

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.