


KEMET Part Number: ALS31A222MF400
(A431PM222M400A)



ALS31, Aluminum Electrolytic, 2,200 uF, 20%, 400 VDC, -40/+85°C



General Information	
Series:	ALS31
Dielectric:	Aluminum Electrolytic
Description:	Screw Terminal, Aluminum Electrolytic
RoHS:	Yes
AEC-Q200:	No
Component Weight:	505 g
Notes:	Dimensions D And L Include Sleevling. MS (MxH) = M12x16.
Shelf Life:	156 Weeks

Dimensions	
D	66mm +/-1mm
L	105mm +/-2mm
T	5.5mm +/-0.5mm
S	28.5mm +/-0.5mm
DT	13mm +/-0.5mm
LT	110.5mm +/-1mm
TD	10mm MIN
V	15.8mm NOM
Z	10mm NOM

Specifications	
Capacitance:	2,200 uF
Capacitance Tolerance:	20%
Voltage DC:	400 VDC, 440 VDC (Surge)
Temperature Range:	-40/+85°C
Rated Temperature:	85°C
Life:	19000 Hrs (Rated Voltage And Ripple Current At 85C), 38000 Hrs (Rated Voltage At 85C)
Resistance:	62 mOhms (100Hz 20C), 44 mOhms (10kHz 20C)
Ripple Current:	11.2 Amps (100Hz 85C), 18.8 Amps (10kHz 85C)
Leakage Current:	5280 uA (5min 20°C)

Packaging Specifications	
Sleevling:	Yes
Packaging:	Bulk, Box

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

