

**KEMET Part Number: C0402C103K4PACTU**  
(C0402C103K4PAC7867)

SMD Comm X5R, Ceramic, 0.01 uF, 10%, 16 VDC, X5R, SMD, MLCC, Temperature Stable, Class II, 0402



**Dimensions**

Chip Size		0402
L		1mm +/-0.05mm
W		0.5mm +/-0.05mm
T		0.5mm +/-0.05mm
S		0.3mm MIN
B		0.3mm +/-0.1mm

**Packaging Specifications**

<b>Packaging:</b>	T&R, 180mm, Paper Tape
<b>Packaging Quantity:</b>	10000

**General Information**

<b>Series:</b>	SMD Comm X5R
<b>Style:</b>	SMD Chip
<b>Description:</b>	SMD, MLCC, Temperature Stable, Class II
<b>Features:</b>	Temperature Stable, Class II
<b>RoHS:</b>	Yes
<b>Termination:</b>	Tin
<b>Marking:</b>	No
<b>AEC-Q200:</b>	No
<b>Component Weight:</b>	1210 ug
<b>Shelf Life:</b>	78 Weeks
<b>MSL:</b>	1

**Specifications**

<b>Capacitance:</b>	0.01 uF
<b>Measurement Condition:</b>	1 kHz 1.0Vrms
<b>Capacitance Tolerance:</b>	10%
<b>Voltage DC:</b>	16 VDC
<b>Dielectric Withstanding Voltage:</b>	40 VDC
<b>Temperature Range:</b>	-55/+85°C
<b>Temperature Coefficient:</b>	X5R
<b>Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC):</b>	15%, 1kHz 1.0Vrms
<b>Dissipation Factor:</b>	5% 1 kHz 1.0Vrms
<b>Aging Rate:</b>	5% Loss/Decade Hour: Referee Time is 48 Hours
<b>Insulation Resistance:</b>	100 GOhms