

**KEMET Part Number: C0603C334Z4VACTU**  
(C0603C334Z4VAC7867)

**KEMET**  
a YAGEO company

SMD Comm Y5V, Ceramic, 0.33 uF, -20/+80%, 16 VDC, Y5V, SMD, MLCC, General Purpose, Class III, 0603



#### Dimensions

Dimensions	
Chip Size	0603
L	1.6mm +/-0.15mm
W	0.8mm +/-0.15mm
T	0.8mm +/-0.10mm
S	0.7mm MIN
B	0.35mm +/-0.15mm

#### Packaging Specifications

Packaging:	T&R, 180mm, Paper Tape
Packaging Quantity:	4000

#### General Information

Series:	SMD Comm Y5V
Style:	SMD Chip
Description:	SMD, MLCC, General Purpose, Class III
Features:	Class III
RoHS:	Yes
Termination:	Tin
Marking:	No
AEC-Q200:	No
Component Weight:	6500 ug
Shelf Life:	78 Weeks
MSL:	1

#### Specifications

Capacitance:	0.33 uF
Measurement Condition:	1 kHz 1.0Vrms
Capacitance Tolerance:	-20/+80%
Voltage DC:	16 VDC
Dielectric Withstanding Voltage:	40 VDC
Temperature Range:	-30/+85°C
Temperature Coefficient:	Y5V
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC):	+22%/ -82%, 1kHz 1.0Vrms
Dissipation Factor:	7% 1 kHz 1.0Vrms
Aging Rate:	7% Loss/Decade Hour: Referee Time is 1000 Hours
Insulation Resistance:	303 MOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

**KEMET**  
a YAGEO company