

SMD Comm X7R HV, Ceramic, 0.047 uF, 10%, 1500 VDC, X7R, SMD, MLCC, High Voltage, Temperature Stable, 2225



Dimensions

Chip Size		2225
L		5.6mm +/-0.4mm
W		6.4mm +/-0.4mm
T		1.6mm +/-0.20mm
B		0.6mm +/-0.35mm

Packaging Specifications

Packaging:	T&R, 330mm, Plastic Tape
Packaging Quantity:	4000

General Information

Series:	SMD Comm X7R HV
Style:	SMD Chip
Description:	SMD, MLCC, High Voltage, Temperature Stable
Features:	High Voltage
RoHS:	Yes
Termination:	Tin
Marking:	No
AEC-Q200:	No
Component Weight:	430 mg
Shelf Life:	78 Weeks
MSL:	1

Specifications

Capacitance:	0.047 uF
Measurement Condition:	1 kHz 1.0Vrms
Capacitance Tolerance:	10%
Voltage DC:	1500 VDC
Dielectric Withstanding Voltage:	1800 VDC
Temperature Range:	-55/+125°C
Temperature Coefficient:	X7R
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC):	15%, 1kHz 1.0Vrms
Dissipation Factor:	2.5% 1 kHz 1.0Vrms
Aging Rate:	3% Loss/Decade Hour: Referee Time is 1000 Hours
Insulation Resistance:	21.2766 GOhms