


C44A, Film, Metallized Polypropylene, Power, 20 uF, 5%, 250 VAC, 400 VDC



General Information	
<b>Series:</b>	C44A
<b>Dielectric:</b>	Metallized Polypropylene
<b>Style:</b>	Can
<b>RoHS:</b>	With Exemptions
<b>REACH:</b>	SVHC (Pb – CAS 7439-92-1)
<b>Lead:</b>	Threaded Studs M6
<b>AEC-Q200:</b>	No
<b>Miscellaneous:</b>	Thermal Resistance = 6.2 C/W.

Dimensions	
<b>D</b>	45mm +/-0.5mm
<b>L</b>	80mm +/-2mm
<b>S</b>	22.3mm +/-0.5mm

Packaging Specifications	
<b>Mounting:</b>	Bolt - M8x10
<b>Packaging:</b>	Bulk, Bag
<b>Packaging Quantity:</b>	60

Specifications	
<b>Capacitance:</b>	20 uF
<b>Capacitance Tolerance:</b>	5%
<b>Voltage AC:</b>	250 VAC
<b>Voltage DC:</b>	400 VDC
<b>Temperature Range:</b>	-40/+85°C
<b>Rated Temperature:</b>	70°C
<b>Max dV/dt:</b>	30 V/us
<b>Resistance:</b>	5 mOhms (TYP)
<b>Ripple Current:</b>	18 Amps, 600 Amps (Peak)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.