


C44P-R, Film, Metallized Polypropylene, AC Filter, 68 uF, 10%, 640 VAC, 1400 VDC



Dimensions	
D	75mm +/-0.5mm
L	247mm +/-2mm
W	21mm +/-1mm
S	35mm +/-1mm
W1	45mm +/-1mm

Packaging Specifications	
Mounting:	Bolt - M12x16
Packaging:	Bulk, Bag

General Information	
Series:	C44P-R
Dielectric:	Metallized Polypropylene
Style:	Can
Features:	Single Phase PFC
RoHS:	Yes
Lead:	Threaded Studs M10
AEC-Q200:	No
Miscellaneous:	Thermal Resistance = 5.3 C/W.

Specifications	
Capacitance:	68 uF
Capacitance Tolerance:	10%
Voltage AC:	640 VAC
Voltage DC:	1400 VDC
Temperature Range:	-25/+70°C
Rated Temperature:	70°C
Dissipation Factor:	0.02% 25C
Max dV/dt:	30 V/us
Resistance:	1.6340663 mOhms (10kHz)
Ripple Current:	60 Amps (10kHz 40C)
Inductance:	160 nH