


C44U-M, Film, Metallized Polypropylene, DC Link, 950 uF, 10%, 1300 VDC



General Information

Series:	C44U-M
Dielectric:	Metallized Polypropylene
Style:	Can
Features:	DC Filtering, Energy Storage
RoHS:	Yes
Lead:	Screw Terminals M6
AEC-Q200:	No
Miscellaneous:	Thermal Resistance = 1.8 C/W. Weight = 13100 grams.

Dimensions

D	116mm +2mm
L	273mm +/-2mm
L1	276mm +/-2mm
S	50mm +/-0.3mm
D1	119mm +0.5mm

Packaging Specifications

Mounting:	Bolt - M12x16
Packaging:	Bulk, Bag
Packaging Quantity:	4

Specifications

Capacitance:	950 uF
Capacitance Tolerance:	10%
Voltage DC:	1300 VDC
Temperature Range:	-40/+85°C
Rated Temperature:	75°C
Insulation Resistance:	30 MOhms
Max dV/dt:	9 V/us
Resistance:	1.8 mOhms (10kHz)
Ripple Current:	96 Amps (10kHz 40C), 8325 Amps (Peak)
Inductance:	80 nH