


C44A, Film, Metallized Polypropylene, Power, 75 uF, 5%, 250 VAC, 400 VDC



Threaded Mounting Stud
 D < 55: M8x10
 D >= 55: M12x12,5

Dimensions	
D	60mm +/-0.5mm
L	101mm +/-2mm
S	22.3mm +/-0.5mm

Packaging Specifications	
Mounting:	Bolt - M12x12.5
Packaging:	Bulk, Bag
Packaging Quantity:	16

General Information	
Series:	C44A
Dielectric:	Metallized Polypropylene
Style:	Can
RoHS:	Yes
Lead:	Threaded Studs M6
AEC-Q200:	No
Miscellaneous:	Thermal Resistance = 3.2 C/W.

Specifications	
Capacitance:	75 uF
Capacitance Tolerance:	5%
Voltage AC:	250 VAC
Voltage DC:	400 VDC
Temperature Range:	-40/+85°C
Rated Temperature:	70°C
Max dV/dt:	20 V/us
Resistance:	5 mOhms (TYP)
Ripple Current:	30 Amps, 1500 Amps (Peak)