


C4AT, Film, Metallized Polypropylene, Power, 15 uF, 5%, 275 VAC, 450 VDC, 70°C, Lead Spacing = 37.5mm



General Information	
Series:	C4AT
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	Switching
RoHS:	Yes
Lead:	4 Wire Leads
AEC-Q200:	No

Dimensions	
L	42mm NOM
H	45mm NOM
T	30mm NOM
S	37.5mm +/-0.4mm
S1	20.3mm +/-0.4mm
LL	6mm -2mm
F	1.2mm NOM

Specifications	
Capacitance:	15 uF
Capacitance Tolerance:	5%
Voltage AC:	275 VAC
Voltage DC:	450 VDC
Temperature Range:	-40/+85°C
Rated Temperature:	70°C
Dissipation Factor:	0.05%
Max dV/dt:	55 V/us
Resistance:	1.6 mOhms (100kHz)
Ripple Current:	29 Amps (100kHz 70C), 828 Amps (Peak)

Packaging Specifications	
Packaging:	Bulk, Bag
Packaging Quantity:	36

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.