


C4AE, Film, Metallized Polypropylene, DC Link, 22 uF, 5%, 700 VDC, 70°C, Lead Spacing = 37.5mm



Dimensions

L	42mm +0.6/-0.7mm
H	44mm +0.2/-0.7mm
T	24mm +0.4/-0.7mm
S	37.5mm +/-0.4mm
S1	10.2mm +/-0.4mm
LL	6mm -2mm
F	1.2mm NOM
G	0.5mm NOM

Packaging Specifications

Packaging:	Bulk, Box
------------	-----------

General Information

Series:	C4AE
Dielectric:	Metallized Polypropylene
Style:	Radial
RoHS:	Yes
Termination:	Tin
Lead:	4 Wire Leads
AEC-Q200:	No
Component Weight:	22.73 g
Miscellaneous:	Thermal Resistance = 17 C/W.
Notes:	Not for new design – the replacement series is: C4AQ.

Specifications

Capacitance:	22 uF
Capacitance Tolerance:	5%
Voltage DC:	700 VDC
Temperature Range:	-40/+85°C
Rated Temperature:	70°C
Insulation Resistance:	1.36 GOhms
Max dV/dt:	13 V/us
Resistance:	4.3 mOhms (10kHz 70C)
Ripple Current:	13 Amps (10kHz 70C), 288 Amps (Peak)
Inductance:	30 nH