


C4AF, Film, Metallized Polypropylene, Power, 62 uF, 10%, 250 VAC, 500 VDC, 85°C, Lead Spacing = 52.5mm



General Information	
Series:	C4AF
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	Harsh Environmental Conditions
RoHS:	Yes
Lead:	4 Wire Leads
Qualifications:	AEC-Q200, IEC61071, EN61071, VDE0560
AEC-Q200:	Yes
Miscellaneous:	Rth = 7 C/W.

Dimensions	
L	57.5mm +0.8/-0.7mm
H	65mm +0.3/-0.7mm
T	45mm +0.5/-0.7mm
S	52.5mm +/-0.4mm
S1	20.3mm +/-0.4mm
LL	6mm +0/-2mm
F	1.2mm +/-0.05mm

Specifications	
Capacitance:	62 uF
Capacitance Tolerance:	10%
Voltage AC:	250 VAC
Voltage DC:	500 VDC
Temperature Range:	-55/+105°C
Rated Temperature:	85°C
Dissipation Factor:	0.07% MAX
Insulation Resistance:	480 MOhms
Max dV/dt:	18 V/us
Resistance:	2.4 mOhms
Ripple Current:	36.5 Amps Irms (MAX), 1116 Amps Ipk
Inductance:	45 nH (ESL)

Packaging Specifications	
Packaging:	Bulk, Box
Packaging Quantity:	18

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.