


**KEMET Part Number: CA064X473K3RACTU**  
(CA064X473K3RAC7800)

Array Comm X7R Flex, Ceramic, 0.047 uF, 10%, 25 VDC, X7R, SMD, MLCC, Array, Flex Termination, Class II, 0612



General Information	
<b>Series:</b>	Array Comm X7R Flex
<b>Style:</b>	SMD Array
<b>Description:</b>	SMD, MLCC, Array, Flex Termination, Class II
<b>RoHS:</b>	Yes
<b>Termination:</b>	Flexible Termination
<b>AEC-Q200:</b>	No
<b>Chip Size:</b>	0612
<b>Shelf Life:</b>	78 Weeks
<b>MSL:</b>	1

Dimensions	
<b>L</b>	1.6mm +/-0.2mm
<b>W</b>	3.2mm +/-0.2mm
<b>T</b>	0.8mm +/-0.10mm
<b>P</b>	0.8mm +/-0.10mm

Packaging Specifications	
<b>Packaging:</b>	T&R, 180mm, Paper Tape
<b>Packaging Quantity:</b>	4000

Specifications	
<b>Capacitance:</b>	0.047 uF
<b>Measurement Condition:</b>	1 kHz 1.0Vrms
<b>Capacitance Tolerance:</b>	10%
<b>Voltage DC:</b>	25 VDC
<b>Dielectric Withstanding Voltage:</b>	62.5 VDC
<b>Temperature Range:</b>	-55/+125°C
<b>Temperature Coefficient:</b>	X7R
<b>Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC):</b>	15%, 1kHz 1.0Vrms
<b>Dissipation Factor:</b>	3.5% 1kHz 1.0Vrms
<b>Aging Rate:</b>	3% Loss/Decade Hour: Referee Time is 1000 Hours
<b>Insulation Resistance:</b>	21.277 GOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.