

C4AQ, Film, Metallized Polypropylene, Automotive DC Link, 10 uF, 10%, 500 VDC, 70°C, Lead Spacing = 27.5mm



General Information	
Series:	C4AQ
Dielectric:	Metallized Polypropylene
Style:	Radial
RoHS:	Yes
Lead:	Wire Leads
Qualifications:	AEC-Q200, IEC61071, EN61071, VDE0560
AEC-Q200:	Yes
Miscellaneous:	Rth = 36 C/W.

Dimensions	
L	31.5mm +0.5/-0.7mm
H	25mm +0.2/-0.7mm
T	13mm +0.3/-0.7mm
S	27.5mm +/-0.4mm
LL	6mm +0/-2mm
F	0.8mm +/-0.05mm

Specifications	
Capacitance:	10 uF
Capacitance Tolerance:	10%
Voltage DC:	500 VDC
Temperature Range:	-55/+105°C
Rated Temperature:	70°C
Dissipation Factor:	0.02% (10 kHz 25C)
Insulation Resistance:	3 GOhms
Max dV/dt:	10 V/us
Resistance:	7.8 mOhms (10kHz 70C)
Ripple Current:	9.6 Amps Irms (10kHz 70C), 96 Amps Ipk
Inductance:	22 nH

Packaging Specifications	
Packaging:	Bulk, Box
Packaging Quantity:	234