

C4AT, Film, Metallized Polypropylene, Power, 3.3 uF, 5%, 275 VAC, 450 VDC, 70°C, Lead Spacing = 27.5mm



**Dimensions**

L	32mm -0.7mm
H	33mm -0.7mm
T	18mm -0.7mm
S	27.5mm +/-0.4mm
S1	5.1mm +/-0.4mm
LL	6mm -2mm
F	1.2mm NOM

**Packaging Specifications**

Packaging:	Bulk, Bag
Packaging Quantity:	80

**General Information**

Series:	C4AT
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	Switching
RoHS:	Yes
Lead:	4 Wire Leads
AEC-Q200:	No
Component Weight:	28.88 g

**Specifications**

Capacitance:	3.3 uF
Capacitance Tolerance:	5%
Voltage AC:	275 VAC
Voltage DC:	450 VDC
Temperature Range:	-40/+85°C
Rated Temperature:	70°C
Dissipation Factor:	0.05%
Max dV/dt:	82 V/us
Resistance:	2.9 mOhms (100kHz)
Ripple Current:	21 Amps (100kHz 70C), 269 Amps (Peak)