

KEMET Part Number: CKC33C472JJGACTU
(CKC33C472JJGAC7800)



KC Link Comm C0G, Ceramic, 4700 pF, 5%, 1700 VDC, C0G, SMD, MLCC, Ultra-Stable, Low Loss, Class I, 3640



| General Information | |
|---------------------|--|
| Series: | KC Link Comm C0G |
| Style: | SMD Chip |
| Description: | SMD, MLCC, Ultra-Stable, Low Loss, Class I |
| Features: | Ultra-Stable, Low Loss |
| RoHS: | Yes |
| Termination: | Tin |
| Marking: | No |
| AEC-Q200: | No |
| Shelf Life: | 78 Weeks |
| MSL: | 1 |

| Dimensions | |
|------------|-----------------|
| Chip Size | 3640 |
| L | 9.3mm +/-0.6mm |
| W | 10.2mm +/-0.4mm |
| T | 1.4mm +/-0.15mm |
| B | 1.27mm +/-0.4mm |

| Packaging Specifications | |
|--------------------------|--------------------------|
| Packaging: | T&R, 180mm, Plastic Tape |
| Packaging Quantity: | 250 |

| Specifications | |
|---|------------------------|
| Capacitance: | 4700 pF |
| Measurement Condition: | 1 kHz 1.0Vrms |
| Capacitance Tolerance: | 5% |
| Voltage DC: | 1700 VDC |
| Dielectric Withstanding Voltage: | 2040 VDC |
| Temperature Range: | -55/+150°C |
| Temperature Coefficient: | C0G |
| Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC): | 30 ppm/C, 1kHz 1.0Vrms |
| Dissipation Factor: | 0.1% 1 kHz 1.0Vrms |
| Aging Rate: | 0% Loss/Decade Hour |
| Insulation Resistance: | 100 GOhms |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

