

F161, Film, Metallized Polyester Stacked, Automotive Grade, 0.22 uF, 10%, 40 VAC, 63 VDC, 85°C, 4036, 5.5mm



Note: '()' correspond to the letters used in the product bulletin

Dimensions	
Chip Size	4036
L	10.2mm +/-0.2mm
W	9.1mm +/-0.2mm
T	5.5mm +/-0.2mm
F	0.5mm NOM

Packaging Specifications	
Packaging:	T&R
Packaging Quantity:	800

General Information	
Series:	F161
Dielectric:	Metallized Polyester Stacked
Style:	SMD Chip
Features:	Automotive Grade
RoHS:	Yes
Qualifications:	AEC-Q200
AEC-Q200:	Yes

Specifications	
Capacitance:	0.22 uF
Capacitance Tolerance:	10%
Voltage AC:	40 VAC
Voltage DC:	63 VDC
Temperature Range:	-55/+125°C
Rated Temperature:	85°C
Dissipation Factor:	0.8% 1kHz, 1.2% 10kHz, 3% 100kHz
Insulation Resistance:	1 GOhms
Max dV/dt:	20 V/us