


KEMET, FLLD3-MH, EMI/RFI Filters, Noise Suppression, 520 VAC, 42 A, 280x50x85mm



General Information	
Series:	FLLD3-MH
Style:	Chassis Mount
Description:	EMI Filter, Chassis Mount, Motor Drives
Features:	Three Phase, High Performance, High Voltage
RoHS:	Yes
Qualifications:	IEC/EN 60939, UL 1283
Lead:	Threaded Studs M6

Dimensions	
L	280mm NOM
W	50mm NOM
H	85mm NOM
L1	295mm NOM
L2	310mm NOM
W1	30mm NOM
J	30mm NOM
K	5.5mm NOM
M (Earth)	Threaded Studs M6
Lead	Threaded Studs M6

Specifications	
Voltage AC:	520 VAC, 300 VAC
Rated Frequency:	50-60 Hz
Ripple Current:	42 A (50°C)
Rated Temperature:	50°C
Temperature Range:	-25/+100°C
Climate Category:	25/100/21
Test Voltage DC (P to P):	2250 VDC
Test Voltage DC (P to E):	3000 VDC
Voltage:	2250 VDC (Test P to P), 3000 VDC (Test P to E)
Power Loss:	15 W (25°C 50 Hz)
Leakage Current:	4.7 mA

Packaging Specifications	
Packaging:	Bulk
Packaging Quantity:	1
Weight:	1.4 kg

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.