


KEMET, FLLD3-PV, EMI/RFI Filters, Noise Suppression, 520 VAC, 1 kA, 350x230x170mm



General Information	
Series:	FLLD3-PV
Style:	Chassis Mount
Description:	EMI Filter, Chassis Mount, With Y Capacitor
Features:	Three Phase, High Performance, High Voltage
RoHS:	Yes
Qualifications:	IEC/EN 60939, UL 1283
Lead:	Threaded Studs M12

Dimensions	
L	350mm NOM
W	230mm NOM
H	170mm NOM
L1	145mm NOM
W1	255mm NOM
W2	280mm NOM
U	60mm NOM
X	8mm NOM
Y	40mm NOM
Z	55mm NOM
I	20mm NOM
N	14mm NOM
M (Earth)	Threaded Studs M12
Lead	Threaded Studs M12

Specifications	
Voltage AC:	520 VAC
Voltage:	2250 VDC (Test P to P), 3000 VDC (Test P to E)
Rated Frequency:	50-60 Hz
Ripple Current:	1000 A (50°C)
Rated Temperature:	50°C
Temperature Range:	-40/+100°C
Climate Category:	40/100/21
Test Voltage DC (P to P):	2250 VDC
Test Voltage DC (P to E):	3000 VDC
Power Loss:	75 W (25°C 50 Hz)
Leakage Current:	5 mA (MAX)

Packaging Specifications	
Packaging:	Bulk
Packaging Quantity:	1
Weight:	17 kg

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.