


KEMET Part Number: FM0H224ZF
(USCFM00H224Z00)

FM, Supercapacitors, Radial Molded, 0.22 F, -20/+80%, 5.5 VDC, Wire Leads, Lead Spacing = 5mm



Dimensions	
W	10.5mm +/-0.5mm
H	11.5mm +/-0.5mm
T	6.5mm +/-0.5mm
S	5mm +/-0.5mm
LL	5mm +/-1mm
G	0.4mm +/-0.1mm
LT1	0.5mm +/-0.1mm
LT2	0.4mm +/-0.1mm

Packaging Specifications	
Lead:	Wire Leads
Weight:	1.6 g
Packaging:	Bulk, Box
Packaging Quantity:	1000

General Information	
Series:	FM
Description:	Radial Molded Double Layer Capacitor
RoHS:	Yes
AEC-Q200:	No
Miscellaneous:	DischargeValue = 0.22 F.

Specifications	
Capacitance:	0.22 F
Capacitance Tolerance:	-20/+80%
Voltage DC:	5.5 VDC
Temperature Range:	-25/+70°C
Rated Temperature:	70°C
Resistance:	100000 mOhms (1kHz)
Ripple Current:	0.33 mAmps (30min)