


KEMET Part Number: MR-4
(USEZ4000000000)

KEMET, MR, Current, Round - Toroidal, Zero Phase, High Sensitivity, Compact



General Information	
Series:	MR
Type:	Current
Style:	Round - Toroidal
Description:	Zero-Phase Current Transformers
Features:	High Sensitivity, Compact
Lead:	Cables
RoHS:	Yes
Notes:	Measurement Conditions: f=60Hz, R=300 Ohms, I _o =22.5 mAmps

Dimensions	
D	16.5mm MIN
H	10.8mm MAX
D2	32mm MAX
D3	34.5mm MAX
D4	7mm NOM
LL	67mm +/-3mm

Specifications	
Temperature Range:	-20/+80°C
Voltage DC:	8 mV MIN (Output)
Current:	125 Amps
Resistance:	30 Ohms
Miscellaneous:	Overinput characteristics (After DC5A input) = 10% MAX.

Packaging Specifications	
Packaging:	Tray
Packaging Quantity:	300
Weight:	16.5 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.