


**KEMET Part Number: PME261JC5470KR30**  
(P561CE473K500A)

**KEMET**

a YAGEO company

PME261/P561, Film, Metallized Paper, General Purpose, 0.047 uF, 10%, 1000 VDC, 85°C, Lead Spacing = 20.3mm



#### General Information

<b>Series:</b>	PME261/P561
<b>Dielectric:</b>	Metallized Paper
<b>Style:</b>	Radial
<b>Features:</b>	Pulse in DC and low frequency applications
<b>RoHS:</b>	Yes
<b>Lead:</b>	Wire Leads
<b>AEC-Q200:</b>	No
<b>Construction:</b>	Molded
<b>Miscellaneous:</b>	AC Operation: 70C MAX.

#### Dimensions

<b>L</b>	24mm -0.5mm
<b>H</b>	14mm -0.5mm
<b>T</b>	7.6mm -0.5mm
<b>S</b>	20.3mm +/-0.4mm
<b>LL</b>	30mm +5mm
<b>F</b>	0.8mm +/-0.05mm

#### Specifications

<b>Capacitance:</b>	0.047 uF
<b>Capacitance Tolerance:</b>	10%
<b>Voltage AC:</b>	500 VAC
<b>Voltage DC:</b>	1000 VDC
<b>Temperature Range:</b>	-40/+100°C
<b>Rated Temperature:</b>	85°C
<b>Dissipation Factor:</b>	1.3% 1kHz
<b>Insulation Resistance:</b>	12 GOhms
<b>Max dV/dt:</b>	2000 V/us

#### Packaging Specifications

<b>Packaging:</b>	Bulk, Bag
<b>Packaging Quantity:</b>	250

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

**KEMET**

a YAGEO company