

**KEMET Part Number: PHE844RR7150MR06L2**  
(F844RM155M440C, PHE844RR7150MR03R06L2)

**KEMET**

a YAGEO company

PHE844/F844, Film, Metallized Polypropylene, Safety, 1.5 uF, 20%, 440 VAC (X1) (ENEC), 480 VAC (UL, cUL), 1000 VDC, 105°C, Lead Spacing = 37.5mm



**Dimensions**

L	41mm MAX
H	36mm MAX
T	19mm MAX
S	37.5mm +/-0.5mm
LL	6mm -1mm
F	1mm +/-0.05mm

**Packaging Specifications**

<b>Packaging:</b>	Tray
<b>Packaging Quantity:</b>	91

**General Information**

<b>Series:</b>	PHE844/F844
<b>Dielectric:</b>	Metallized Polypropylene
<b>Style:</b>	Radial
<b>Features:</b>	EMI Safety
<b>RoHS:</b>	Yes
<b>Lead:</b>	Wire Leads
<b>Safety Class:</b>	X1
<b>Qualifications:</b>	ENEC, UL, cUL
<b>AEC-Q200:</b>	No
<b>THB Performance:</b>	Yes
<b>Component Weight:</b>	25.65 g
<b>Miscellaneous:</b>	ClimCat: 40/105/56/B.

**Specifications**

<b>Capacitance:</b>	1.5 uF
<b>Capacitance Tolerance:</b>	20%
<b>Voltage AC:</b>	440 VAC (X1) (ENEC), 480 VAC (UL, cUL)
<b>Voltage DC:</b>	1000 VDC
<b>Temperature Range:</b>	-40/+105°C
<b>Rated Temperature:</b>	105°C
<b>Dissipation Factor:</b>	0.1% 1kHz, 0.8% 10kHz
<b>Insulation Resistance:</b>	6.6667 GOhms
<b>Max dV/dt:</b>	100 V/us

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

**KEMET**

a YAGEO company