

KEMET Part Number: R413I222050T0K
(413I222050T0K)

KEMET

a YAGEO company

R41T, Film, Metallized Polypropylene, Automotive Safety, 0.022 uF, 10%, 300 VAC (Y2), 125°C, Lead Spacing = 15mm



General Information

Series:	R41T
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	Automotive Grade, EMI Safety
RoHS:	Yes
Lead:	Wire Leads
Safety Class:	Y2
Qualifications:	AEC-Q200, ENEC, UL, cUL, CQC
AEC-Q200:	Yes

Dimensions

L	18mm +0.3/-0.5mm
H	13.5mm +0.1/-0.5mm
T	7.5mm +0.2/-0.5mm
S	15mm +/-0.4mm
LL	25mm +2/-1mm
F	0.6mm +/-0.05mm

Specifications

Capacitance:	0.022 uF
Capacitance Tolerance:	10%
Voltage AC:	300 VAC (Y2)
Temperature Range:	-40/+125°C
Rated Temperature:	125°C
Dissipation Factor:	0.3% 1kHz
Insulation Resistance:	100 GOhms
Max dV/dt:	600 V/us

Packaging Specifications

Packaging:	Bulk, Bag
Packaging Quantity:	700

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

KEMET

a YAGEO company