

**KEMET Part Number: R413N247050T0K**  
(413N247050T0K)

**KEMET**

a YAGEO company

R41T, Film, Metallized Polypropylene, Automotive Safety, 0.047 uF, 10%, 300 VAC (Y2), 125°C, Lead Spacing = 22.5mm



#### General Information

<b>Series:</b>	R41T
<b>Dielectric:</b>	Metallized Polypropylene
<b>Style:</b>	Radial
<b>Features:</b>	Automotive Grade, EMI Safety
<b>RoHS:</b>	Yes
<b>Lead:</b>	Wire Leads
<b>Safety Class:</b>	Y2
<b>Qualifications:</b>	AEC-Q200, ENEC, UL, cUL, CQC
<b>AEC-Q200:</b>	Yes

#### Dimensions

<b>L</b>	26.5mm +0.3/-0.5mm
<b>H</b>	15mm +0.1/-0.5mm
<b>T</b>	6mm +0.2/-0.5mm
<b>S</b>	22.5mm +/-0.4mm
<b>LL</b>	25mm +2/-1mm
<b>F</b>	0.8mm +/-0.05mm

#### Specifications

<b>Capacitance:</b>	0.047 uF
<b>Capacitance Tolerance:</b>	10%
<b>Voltage AC:</b>	300 VAC (Y2)
<b>Temperature Range:</b>	-40/+125°C
<b>Rated Temperature:</b>	125°C
<b>Dissipation Factor:</b>	0.3% 1kHz
<b>Insulation Resistance:</b>	100 GOhms
<b>Max dV/dt:</b>	500 V/us

#### Packaging Specifications

<b>Packaging:</b>	Bulk, Bag
<b>Packaging Quantity:</b>	500

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

**KEMET**

a YAGEO company