

KEMET Part Number: R463R433000M2M
(463R433000M2M)

R46 310 VAC, Film, Metallized Polypropylene, Safety, 3.3 uF, 20%, 310 VAC (X2), 630 VDC, 110°C, Lead Spacing = 27.5mm



General Information

Series:	R46 310 VAC
Dielectric:	Metallized Polypropylene
Style:	Radial
Features:	EMI Safety
RoHS:	Yes
Lead:	Cut
Safety Class:	X2
Qualifications:	ENEC, UL, cUL, CQC
AEC-Q200:	No

Dimensions

L	32mm +0.3/-0.7mm
H	33mm +0.1/-0.7mm
T	18mm +0.2/-0.7mm
S	27.5mm +/-0.4mm
LL	4mm +2mm
F	0.8mm +/-0.05mm

Specifications

Capacitance:	3.3 uF
Capacitance Tolerance:	20%
Voltage AC:	310 VAC (X2)
Voltage DC:	630 VDC
Temperature Range:	-40/+110°C
Rated Temperature:	110°C
Dissipation Factor:	0.1% 1kHz
Insulation Resistance:	9.0909 GOhms
Max dV/dt:	150 V/us

Packaging Specifications

Packaging:	Tray
Packaging Quantity:	256